



High Pressure Port

High Pressure Port

NOTES
 n1. Lubricate all O-Rings with O2 compatible grease before assembling.
 n2. Test high pressure vessels applying 450bars for 20 seconds.

Pos. No	Title	Part No	Quantity
T4	ASSY OF CHECK VALVE	ORT6125	2
W2	ASSY OF LEFT REGULATOR	ORT6470L	1
W3	ASSY OF RIGHT REGULATOR	ORT6470R	1
W4	ASSY OF LEFT MECHANISM	ORT6480L	1
W5	ASSY OF RIGHT MECHANISM	ORT6480R	1
204	MANIFOLD PLATE	ORT6461	1
210	HANDLE	ORT6467	1
211	HP PORT	ORT6469	1
217	HANDLE TUBE	ORT6482	1
221	UMBILICAL LOCK	ORT6487	1
601	Blanking Plug 3/8"		7
602	Blanking Plug 7/16"		3
611	Knob M6		1
750	Pressure Relieve Valve		2
539a	O-RING BS012		2
539b	O-RING BS013		4
664	SCREW M4x12		5
665	SCREW M4x16		3
700	SCK SCREW M8x16		2

Units of measurement	mm UNLESS OTHERWISE STATED	Mass	4,45 kg	Format	ISO A2	Designed by	A.KUDRIASHOV	Changed by	-	Approved by - date	A.BOGATCHEV	Filename	ORT6160-B1.dwg	Date	16.11.2008	Scale	1:1
Material		Projection				DEEP LIFE LTD Strictly Commercial-in-Confidence, copyright (c) 2008. Copying prohibited except as provided for under written contract with Deep Life Ltd.				Title/Name ASSY OF MANIFOLD		Drawing number ORT6460		Edition B1	Sheet(s) 1/1		